

The power behind competitiveness

Delta UPS – Agilon Family

VX Series, Line-interactive
600/1000/1500VA

Reliable power protection for small business and home office applications

The Agilon VX line-interactive UPS designed with microprocessor control offers reliable and cost-effective power protection for PCs, laptops, POS, and other sensitive electronics used in home offices and small businesses. The integrated Automatic Voltage Regulation (AVR) ensures all electronics are receiving stable power while providing higher availability. The Agilon VX series' LED/ LCD display, auto-shutdown software and other superior features make these units perfect for your data protection.

Reliability

- The integrated AVR (Automatic Voltage Regulation) stabilizes the output voltage for better power quality
- Excellent microprocessor control enables accurate detection of power frequency for higher reliability
- Wide input voltage range allows the UPS to work in harsh electrical environments and reduces battery discharging time
- Batteries are automatically recharged even when the UPS is in off mode and the UPS can start without mains (Cold-Start)
- UPS is able to restart automatically while utility power is recovering
- Surge protection defends your critical load against damage



Convenience

- Several standard IEC 320 output sockets simplify the connectivity to computer and IT peripherals
- Compact size saves more space for critical equipment

Manageability

- Standard USB communication port enhances monitoring and manageability
- Touch screen LCD for a clear display of UPS information (Only applicable for LCD model)
- Advanced UPS management software provides remote shutdown and control



PC



Monitor



ADSL



Home



POS

 **DELTA**
Smarter. Greener. Together.

Delta UPS – Agilon Family

VX Series, Line-interactive
600/1000/1500VA

Technical Specifications				
Model		VX-600VA	VX-1000VA	VX-1500VA
Power Rating		600VA/360W	1000VA/600W	1500VA/900W
Input	Nominal Voltage	230 Vac		
	Voltage Range	170 ~ 280 Vac (full load)		
	Frequency Range	45 ~ 65Hz		
Output	Voltage	230 Vac ± 10% (Battery mode)		
	Frequency Range	50/60 Hz ± 1 Hz		
	Waveform (Batt. Mode)	Simulated Sinewave		
	Receptacle	IEC 320 C13 x 4	IEC 320 C13 x 4	IEC 320 C13 x 4
Battery	Battery Type & Number	12V/7 Ah x 1	12V/7 Ah x 2	12V/7 Ah x 2
	Recharge Time	6 ~ 8 hours to 90%		
	Cold Start	Yes		
Indicator		LED	LCD	
Communication Interfaces	Standard	USB Port x 1		
Environment	Operating Temperature	0 ~ 40°C		
	Altitude	0 ~ 1000m		
	Relative Humidity	0 ~ 95% (non-condensing)		
Audible Noise		< 40 dB		< 45 dB
Conformance	Safety	CE		
Physical	Dimensions (W x D x H)	101 x 279 x 142 mm	130 x 320 x 182 mm	
	Net Weight	4.2 kg	8.2 kg	9.7 kg

All specifications are subject to change without prior notice.



600VA rear view




1000VA rear view



1500VA rear view



Delta offers a full range of UPS solutions from 600 VA to 4000 kVA to fulfill your power security needs.



2007~ 2008 Forbes Asia's Fabulous 50



2009 Frost & Sullivan Green Excellence Award for Corporate Leadership



Delta's Manufacturing System is Certified by ISO 9001 and ISO 14001 Standards



IECQ Certificate of Hazardous Substance Process Management

