

Modular Rack

Data Center Rack & Accessories

The Backbone of Data Center Excellence

Optimize your data center with Delta's modular racks: a reliable foundation for your IT infrastructure. With 70% perforation for superior heat dissipation and unmatched design flexibility, they adhere to EIA-310 industry standard for seamless integration and peak performance.



Convenience

- Tool-less door installation and reversible design
- Simplify cable management with removable power trough and tool-less roof cable ports
- Removable bottom cover enables cable access through the raised floor
- Front and rear doors open up to 130° for convenient installation and repair
- Low profile casters for easy deployment and mobility
- Fast deployment leveling feet for quick setup and versatility
- Seamless rack integration for a clean and secure data room layout

Flexibility

- Split rear doors optimize space and streamline maintenance
- Adjustable mounting rails for customized installations
- 4 universal mounting brackets facilitate versatile installations
- Comprehensive range of accessories for a well-organized data room

Safety

- Durable frame supports up to 1420 kg with IP20 rating
- Grounded doors with locks for security
- Adjustable leveling feet ensure stability

Technical Specifications

Model	SR3110	SR1110	SR3160	SR1160
PHYSICAL				
Dimensions (W x D x H)	800 (19") x 1100 x 2000 mm	600 x 1100 x 2000 mm	800 (19") x 1200 x 2000 mm	600 x 1200 x 2000 mm
Net Weight	150 kg	137 kg	160 kg	150 kg
Packing Dimensions (W x D x H)	830 x 1160 x 2156 mm	630 x 1160 x 2156 mm	830 x 1260 x 2156 mm	630 x 1260 x 2156 mm
ENVIRONMENT				
Operating Temperature	0 to 40°C			
Operating Humidity	0-95%			
Altitude	0-3000 m			
Storage Temperature	-15 to 50°C			
CONFORMANCE				
Ingress Protection	IP20			
Rack Standards	EIA-310-D			
Safe Grounding	UL 60950 (max. 63A)			
Sustainability	RoHS			

All specifications are subject to change without prior notice.

Optional Accessory

P/N	Description	Rack Compatibility			
		SR3110	SR1110	SR3160	SR1160
SR6001	Bottom Cover for W600 x D1200 Rack Cabinet				●
SR7001	1U Horizontal Cable Management Channel	●	●	●	●
SR7002	Vertical Cable Management Channel	●	●	●	●
SR7003	Cable Ladder, 300 mm	●	●	●	●
SR7004	Ring Type Wire Holder (10 pcs/per box)	●	●	●	●
SR8001	Power Cable Trough with Through-Hole, 800 mm	●		●	
SR8002	Cable Trough with Through-Hole, 800 mm	●		●	
SR8003	Bottom Cover for W800 x D1100 Rack Cabinet	●			
SR8006	Bottom Cover for W800x D1200 Rack Cabinet			●	
SR9001	Power Cable Trough with Through-Hole, 600 mm		●		●
SR9002	Cable Trough with Through-Hole, 600 mm		●		●
SR9003	Bottom Cover for W600 x D1100 Rack Cabinet		●		●
SR9004	1U Fixed Shelf	●	●	●	●
SR9005	1U Sliding Shelf	●	●	●	●
SR9006	1U Blanking Panel (10 pcs/per box)	●	●	●	●
SR9007	2U Blanking Panel (10 pcs/per box)	●	●	●	●



1U Horizontal Cable Management Channel



Vertical Cable Management Channel



Cable Ladder



Power Cable Trough with Through Hole



Cable Trough with Through Hole



Bottom Cover



1U Fixed Shelf



1U Sliding Shelf



1U Blanking Panel



2U Blanking Panel



Delta Data Center



Delta ICT LinkedIn



Delta ICT YouTube

