



顯示	E		
連線	輸入 1:	EC30	6 30P
	輸入 2:	EC30	6 30P
	輸出:	EC30	6 30
通訊介面	MP		
操作溫度	0~40°C		
	°C		
噪音(1 公尺處)	40		
尺寸(高 寬 深)	43	440	3 5
重量	7.7		

• 所有產品規格若需變更，恕不另行通知。



a

