

The power behind competitiveness

Delta UPS – Modulon Family

DPH Series, Three Phase
50 - 300/500/600 kVA

The world's highest power density providing ultimate MW power protection with leading power performance and superior reliability

In this IT intensive world with heavy data traffic driven by cloud, 4G/5G and media streaming applications, IT managers are facing the challenges of increasing rack power density and limited data center space. Delta's innovative modular UPS technologies provide the answer to customers' demand for high power density, high power performance, and ultimate availability. The brand-new Delta Modulon DPH series UPS 50-300/500/600kVA achieves the industry's leading power density of 50kW per module, offering the smallest footprint and best space utilization. The Modulon DPH Series UPS is the ideal modular power protection for MW data centers to achieve total cost of ownership (TCO) optimization.

Excellent Power Performance

- The industry's leading power density per module at 50kW in 3U space, and the smallest footprint for 500kVA in a single rack and 600kVA in two racks, to achieve the best utilization compared with its peers
- High AC-AC efficiency up to 96.5% and ECO mode to 99% resulting in marked energy cost savings
- Green mode featuring a load aggregation function optimizes system efficiency

Ultimate Availability

- Fully modularized design and hot-swappable key modules ensure Mean Time To Repair (MTTR) close to zero without downtime risk
- Redundant components and dual CAN bus delivers highest system availability and avoids single point of failure
- Modular UPS grows with your business by parallel expansion up to 8 units for 4.8MVA of total power capacity

High Manageability

- User-friendly 10" color touch screen enables easy local UPS management
- Environment information such as security, water, fire, and temperature can be integrated into the UPS for easy monitoring via the LCD of the UPS
- If the UPS is equipped with an external battery management system, the battery information can be integrated into the UPS and monitored via the LCD of the UPS



Data Center



Telecom



Industrial



Network



Banking



Security



Lab



Medical



Metro



Delta UPS – Modulon Family

DPH Series, Three Phase
50 - 300/500/600 kVA

Technical Specification

Model		DPH-300K	DPH-500K	DPH-600K
Power Rating	kVA	100,150,200,250,300	300,350,400,450,500*	500,550,600
	kW	100,150,200,250,300	300,350,400,450,450	500,550,600
	Power Module Quantity	Up to 6 units	Up to 9 units	Up to 12 units
Input	Nominal Voltage	220/380V, 230/400V, 240/415V (3-phase, 4-wire + G)		
	Voltage Range	305 ~ 478Vac (full load), 228 ~ 478Vac (70% load)		
	Current Harmonic Distortion	< 3%**		
	Power Factor	> 0.99		
	Frequency Range	40 ~ 70 Hz		
Output	Voltage	220/380V, 230/400V, 240/415V (3-phase, 4-wire + G)		
	Voltage Harmonic Distortion	≤ 0.5% (linear load)		
	Voltage Regulation	±1% (static)		
	Frequency	50/60 ± 0.05 Hz		
	Overload Capability	≤ 125% : 10 minute ; ≤ 150% : 1 minute ; >150%: 1 second		
Display		10" color touch screen		
Interface	Standard	RS232 x 1, Parallel port x 4, USB type A x 2, USB type B x 1, MODBUS x 1, Smart slot x 1, REPO x 1, EPO x 1, Input dry contact x 4, Output dry contact x 6, External battery temperature detection x 4, External switch/breaker status dry contact x 4, BMS (RJ45) x 1, Ethernet x 1		
	Optional	Relay I/O card, Battery cabinet temperature sensor cable		
Conformance	Safety	CE		
Efficiency	AC-AC Mode	Up to 96.5%		
	ECO Mode	99%		
Battery	Nominal Voltage	±240 Vdc (default, ±180Vdc to ±276Vdc configurable)		
	Charge Voltage	±272V (adjustable from 204V to 312V)		
	Protection of Battery Deep Discharge	Yes		
Environment	Operating Temperature	0 ~ 40°C		
	Relative Humidity	0 ~ 90% (non-condensing)		
	Audible Noise (at one meter)	< 75 dB	< 80 dB	< 85 dB
	IP Protection	IP20		
Others	Parallel Redundancy and Expansion	Module and system redundancy ; Maximum 8 units		
	Emergency Power Off	Remote (default) and local (optional)		
	Battery Start	Yes		
Physical	Dimensions (W x D x H)	600 x 1100 x 2000 mm		1200 x 1100 x 2000 mm
	Weight : UPS System (without power modules)	311 kg	317 kg	605 kg
	Weight : 50kW Power Module (optional)	36 kg		

* The power module's power rating is adjustable to either 50kVA or 55.6kVA via touch panel.

** When input vTHD is less than 1%.

All specifications are subject to change without prior notice.



50kW in 3U space



User-friendly 10" color touch screen



Fully modularized and hot-swappable design



DPH 300 system is inbuilt with four breakers for easy operation and maintenance



DPH 500-600K model is highly integrated with four built-in switches