

The power behind competitiveness

# Delta UPS-Modulon Family

NH Plus Series, Three Phase

20kVA - 480kVA

## Power to build a lasting competitive advantage

The Modulon NH Plus series is Delta's next generation UPS featuring high efficiency, hot-swappable modular structure and N+X redundancy. With its industry leading 94% high efficiency, the NH Plus series delivers remarkably low total cost of ownership in terms of both capital expense and operating expense. With N+X module and system redundancy to guarantee reliability and availability, the Modulon NH Plus series sets a new milestone for UPS protection in mission critical applications.

### Availability

- Available from 20 to 480 kVA (4 units x 120 kVA in parallel).
- Redundancy at module and system level.
- Hot-swappable function ensures uninterrupted operations during maintenance.
- Redundant auxiliary power and control circuit ensures higher reliability.
- Inbuilt maintenance and static bypass switch.

### Flexibility

- Modular design provides easy maintenance and scalability.
- Multi-language LCD display and LED status indicators.
- Two smart slots and six programmable dry contact outputs.
- Optional external battery cabinet for longer backup time.

### Low Total Cost Of Ownership

- Low harmonic distortion (iTHD<3%) optimized generator size to save initial investment
- High input and output power factor (I/P pf >0.99; O/P pf up to 0.9) and 94% high efficiency reduce operating costs



Data Center



Telecom



Industrial



Network



Security



Lab



Medical



Metro



# Delta UPS-Modulon Family

NH Plus Series, Three Phase  
20kVA - 480kVA

Technical Specifications								
Model		NHP-20K	NHP-40K	NHP-60K	NHP-80K	NHP-100K	NHP-120K	
Power Rating - kVA		20	40	60	80	100	120	
Power Rating - kW*		18	36	54	72	90	108	
Input	Nominal Voltage	380/220, 400/230, 415/240 Vac (3 phase, 4-wire + G)						
	Voltage Range	208 ~ 477 Vac (line-line)/120 ~ 276 Vac (line-neutral) **						
	Current Harmonic Distortion	< 3% (full load)						
	Power Factor	> 0.99						
	Frequency	50 or 60 ± 5 Hz						
Output	Voltage	380/220, 400/230, 415/240 Vac (3 phase, 4-wire + G)						
	Voltage Harmonic Distortion	< 3% (linear load)						
	Voltage Regulation	± 1% (static)						
	Frequency	50 or 60 Hz						
	Frequency Regulation	± 0.05 Hz (Internal oscillator) ± 5 Hz (sy(Internal Oscillator)ble in steps of 0.1 Hz)						
	Overload Capability	≤ 125%: 10 minutes; ≤ 150%: 1 minute						
	Interface	Standard	RS232 x 1, SNMP slot x 2, Dry contact output x 6, Dry contact input x 2,					
		Management Peripherals	Battery cabinet temperature x 4, Battery cabinet status detection x 1, Parallel port x 1, REPO x 1 SNMP card, Modbus card, Relay I/O control card, EnviroProbe, SNMP + 5 ports hub, Battery cabinet temperature sensor, Battery cabinet status cable					
Conformance	Safety & EMC	CE, EN62040-1, EN62040-2 Class A						
Other Features	Parallel Redundancy and Expansion	Module and system redundancy; Maximum 4 units in parallel up to 480 kVA						
	Emergency Power Off	Local and remote						
	SRAM Event Log	500 records						
Efficiency	AC-AC	94%						
	ECO Mode	97%						
Environment	Operating Temperature	0 ~ 40°C						
	Relative Humidity	0 ~ 90% (non-condensing)						
	Audible Noise (at one meter)	65 dBA	68 dBA	70 dBA	70 dBA	72 dBA	73 dBA	
Physical	Dimensions UPS Battery	520 x 910 x 1165 mm			520 x 975 x 1695 mm			
	Cabinet (WxDxH)	520 x 850 x 1165 mm (26 Ah x 40 pcs)			520 x 975 x 1695 mm (40 Ah x 40 pcs)			
	Weight	170 kg	200 kg	230 kg	260 kg	350 kg	380 kg	



Mimic LCD Display



Scalable and Hot-swappable



100-120 kVA + Battery Cabinet



Delta offers full range UPS solutions from 600 VA to 4000 kVA to fulfill your power security needs.

\* Operating temperature is under 25°C and reconfiguration of the UPS is required; Delta provides the configuration service.  
\*\* When input voltage is 208-300/120-173 Vac, the sustainable loading is from 70% to 100% of the UPS capacity.  
All specifications are subject to change without prior notice.



2007~ 2008  
Forbes Asia's  
Fabulous 50



2009  
Frost & Sullivan  
Green Excellence  
Award for Corporate  
Leadership



ISO 9001:2008



OHSAS 18001:2007



ISO 14001:2004

