

The power behind competitiveness

# Delta UPS – Ultron Family

DPS Series, Three Phase  
300 - 1200 kVA

## The Next Generation UPS Answering the Demands of Large Data Centers and Colocations

Delta's superior Ultron DPS series 300 - 1200kVA UPS supports unity output power factor to deliver up to 9.6 MW power capacity to meet the demands for large data centers and colocations that require higher power capacity. The Ultron DPS series guarantees the highest level of system reliability and resiliency by supporting self-detection of key components with pre-warning function, multi-layered redundancy design, and complete power rating coverage. Moreover, the DPS series supports advanced manageability. Key environment parameters, and event analysis can all be monitored via local 10" LCD monitor and remotely. Along with optional battery management software, the DPS series enables users to achieve predictive maintenance and minimize system downtime, while lowering the total cost of ownership (TCO).

### Ultimate Availability

- Supports up to 9.6 MW power capacity with the parallel redundancy and expansion up to 8 units
- Redundancy components and dual CAN bus ensures system availability
- Proactive detection of key component status for early diagnosis on UPS malfunction
- Intelligent battery health diagnosis enables better battery maintenance and replacement
- Advanced event analysis, including 10,000 event logs, waveform capturing and key parameters recording, to detect UPS abnormality and ensure higher availability

### Excellent Performance

- The industry's leading power density and smallest footprint with the design of both top/bottom cable entry and inbuilt switches, which allows you to flexibly utilize the space under the circumstance of high power requirements
- Unity output power factor guarantees no-rating and provides 100% kW
- AC-AC efficiency of up to 96.5% and 99% in ECO mode resulting in marked energy cost savings
- Supports both VRLA and environment-friendly Li-ion batteries

### Sophisticated Manageability and Flexibility

- User-friendly 10" color touch panel simplifies local UPS management
- Environment information, such as security, water, fire, and temperature can be integrated and monitored via the LCD panel of the UPS
- If the UPS is equipped with an external battery management system, the battery information can be integrated and monitored via the LCD panel of the UPS
- Fully front access and modular design of key components shortens the mean time to repair (MTTR)
- Flexible battery quantity of 30-46 pcs achieves optimal battery investment



Data Center



Telecom



Industrial



Network



Banking



Security



Medical



Metro



Government



Education



# Delta UPS – Ultron Family

DPS Series, Three Phase  
300 - 1200 kVA

## Technical Specification

Model		DPS-300k	DPS-400K	DPS-500K	DPS-600K	DPS-800K	DPS-1000K	DPS-1200K
Power Rating	kVA	300	400	500	600	800	1000	1200
	kW	300	400	500	600	800	1000	1200
Input	Nominal Voltage	220/380V, 230/400V, 240/415V (3-phase, 4-wire + G)						
	Voltage Range	176/304~276/478 VAC (full load)						
	Current Harmonic Distortion	<3% (with Full Linear Load); <5% (with Full Non-linear Load)						
	Power Factor	> 0.99						
	Frequency Range	40 ~ 70 Hz						
Output	Voltage	220/380V, 230/400V, 240/415V (3-phase, 4-wire + G)						
	Voltage Harmonic Distortion	<1.5% (Linear Load); <5% (Non-linear Load)						
	Voltage Regulation	±1 (static); ±5 (dynamic)						
	Output Power Factor	1						
	Frequency	50/60Hz (Auto-Selectable)						
Overload Capability	≤ 125%: 10 min ; ≤ 150%: 1 min ; >150%: 1 sec							
Display	10" Color Touch Panel							
Interface	Standard	RS232, Parallel port, USB, Modbus RS485, Input dry contact, Output dry contact, SNMP card inbuilt in touch screen						
	Optional	Relay I/O card, Battery cabinet temperature sensor cable						
Conformance	Safety	CE						
Efficiency	AC-AC Mode	Up to 96.5%						
	ECO Mode	99%						
Battery	Type	VRLA, LiB						
	Charge Current	90A	120A	150A	180A	240A	300A	360A
	Battery Quantity	30 – 46 pcs						
Environment	Operating Temperature	0 ~ 40°C						
	Relative Humidity	0 ~ 95% (non-condensing)						
	Audible Noise	<80 dB						
	IP Protection	IP 20						
Others	Parallel Redundancy and Expansion	Maximum 8 units						
	Emergency Power Off	Remote and local						
Physical	Dimensions (W x D x H)	600 mm*	1200 mm*			1800 mm	2450 mm	
		900 mm	900 mm			900 mm	900 mm	
		2000 mm	2000 mm			2000 mm	2000 mm	
	Weight	515 kg	700 kg	811 kg	970 kg	1270 kg	1850 kg	2000 kg

\* The width is for the cabinet which has four inbuilt switches.



DPS series 300-600kVA is highly integrated with four built-in switches as standard model



Fully front access and modular design of key components simplifies maintenance and shorten the mean time to repair (MTTR)



User-friendly 10" color touch screen



Li-ion Battery-ready