Delta UPS Amplon Family

N Gen3 Series, Single Phase, 1/2/3 kVA

Small and Reliable Power Guardian for Office & Home Critical Appliances

The Amplon N Gen3 Series 1-3 kVA is an online doubleconversion uninterruptible power system (UPS) in a best-inclass compact size tower design. It supplies clean sine-wave input power for IT and other sensitive equipment and prevents work interruption, data loss or equipment damage from voltage sags, spikes, harmonic distortion and other power failures.



High Availability

- Output power factor 0.9 provides more wattage to critical loads
- True online double-conversion topology and zero transfer time to battery mode
- Generator compatibility ensures clean, uninterrupted power to the loads during an extended power outage

Green with Low TCO

- Capable of working in harsh electrical environments with wide I/P voltage range to minimize battery usage
- · Excellent overload capacity allows the overload condition to continue within the timeframe
- AC-AC efficiency up to 90%, and ECO mode efficiency up to 95% for better energy savings

Easy Management

- The intuitive LCD display provides UPS status information with the ability to configure locally
- Supports multiple communication interfaces, including USB port, RS-232 port and Mini slot (option for mini SNMP, mini Modbus and mini relay I/O card) for remote monitoring and configuration
- Battery self-test function ensures early detection of the battery status when batteries need to be replaced





















Rear Panel

1 kVA

2 kVA

3 kVA








- 1 USB port
- 2 RS-232 port
- 3 Input circuit breaker
- 4 AC input
- 6 Mini slot
- Output socket
- Output terminal

LCD



Runtime Table

1 kVA

Load	90 W	180 W	270 W	360 W	450 W	540 W	630 W	720 W	810 W	900 W
Backup Time	57.5	26.9	16.8	11.9	9.1	7.3	6.1	4.3	3.6	3.1

2 kVA

Load	180 W	360 W	540 W	720 W	900 W	1080 W	1260 W	1440 W	1620 W	1800 W
Backup Time	61.1	28.3	17.7	12.5	9.5	7.7	6.5	4.5	3.8	3.3

3 kVA

•										
Load	270 W	540 W	810 W	1080 W	1350 W	1620 W	1890 W	2160 W	2430 W	2700 W
Backup Time	67.1	29.4	18.1	12.5	10.3	8.2	6.9	4.9	4.2	3.6

Unit: min



Technical Specifications

Model		NX-1K	NX-2K	NX-3K						
Topology		Online double-conversion								
Power Rating		1 kVA 2 kVA 3 kVA								
		0.9 kW	1.8 kW	2.7 kW						
INPUT			·							
Nominal Voltage		220/ 230 Vac, 1P2W+PE								
Voltage Range		180-285 Vac (100% load); 120)-180 Vac (60-100% load)							
Frequency		40-70 Hz	, 100 740 (00 100%)							
Power Factor		> 0.99 (100% load)								
Connection		IEC C14	IEC C20							
		ILO 020								
OUTPUT		000(1)/ 000/ 000/ 040 // 450	0W DE							
Nominal Voltage		208 ⁽¹⁾ / 220/ 230/ 240 Vac, 1P2	ZW+PE							
Voltage Regulation		±1%								
requency		50/60 ± 3 Hz								
Total Harmonic Dis	tortion (THDv)	≤ 3% (linear load)								
Power Factor		0.9								
Connection		IEC C13 x4		IEC C13 x4 + Terminal						
Overload Capability		· ·	%: 10 mins.; 111-130%: 30 secs; 131-150%	: 3 secs; > 150%: immediately						
Current Crest Ratio)	3:1								
EFFICIENCY										
Online Mode		Up to 90%								
ECO Mode		Up to 95%								
DATTEDY										
BATTERY Battery Type		VRLA								
Nominal Voltage		24 Vdc	48 Vdc	72 Vdc						
Quantity Runtime	100% load	2 pcs 3.1 mins	4 pcs 3.3 mins	6 pcs 3.6 mins						
Runtime										
01	70% load	6.1 mins	6.5 mins	6.9 mins						
Charge Current		1 A								
COMMUNICATION	INTERFACE									
Display		LCD display with LED indicators								
Port		USB, RS-232, Mini slot								
Audible Alarm		Battery mode, Low battery, Overload, Fault, Bypass mode								
PHYSICAL										
Dimensions (W x D	x H)	145 x 282 x 220 mm	145 x 492 x 220 mm	190 x 421 x 318 mm						
Net Weight		9.2 kg	16.8 kg	27 kg						
Packing Dimension	s (W x D x H)	230 x 360 x 325 mm	230 x 590 x 355 mm	320 x 560 x 460 mm						
Packing Weight		10.3 kg	18.6 kg	28.4 kg						
ENVIRONMENT										
Operating Tempera	aturo	0 to 50 °C (40 to 50 °C do-ra	ting to 70% load)							
Humidity		0 to 50 °C (40 to 50 °C de-rating to 70% load) 20-90% (non-condensing)								
,		< 45 dBA								
Audible Noise ⁽²⁾		< 45 dBA 0-4,000 m (derating 1%/100 m from 1,000-4,000 m)								
Altitude										
Storage Temperature		-20 to 50 °C								
Ingress Protection		IP20								
CONFORMANCE										
Safety		CE, UKCA, TISI, RCM, KC								
EMC		IEC 62040-2								
Sustainability		RoHS, REACH		RoHS, REACH						

⁽¹⁾ De-rating to 70% load

All specifications are subject to change without prior notice.



⁽²⁾ Audible noise test with UPS < 75% load at 25 $^{\circ}\text{C}$ in online mode

Management Solution

UPSentry

- Supports RS-232 & USB communication
- Scheduling shutdown, restart and battery test
- **Event tracking**

ShutdownAgent

• Provides a graceful unattended shutdown of multiple computer systems over a network

SNMP IPv6 (optional)

- Remote UPS management from any workstation through internet or intranet
- UPS and system function configuration from any client (password protected)
- Event logs and data tracking

What's in the Box

Standard Accessories

N Gen3 UPS				
User manual				
USB cable (1.5 m)				
AC input cable (1.5 m)				
Free ShutdownAgent software for local UPS status and shutdown				
Free UPSentry software for remote network management				



← → C ☆ http://192.168.1.100

A NELTA

More Product Information

Optional Accessories

UPS Management Accessories

Mini SNMP IPv6	Manages UPS and system functions securely and adjusts parameters through
(Part number: SCMS100035)	SNMP management stations or Internet Browsers using HTTP forms.
Mini Relay I/O card	Offers 6 relay output contacts to monitor status and 2 input contacts for simple
(Part number: 3915101864-S)	shutdown and battery testing in UPS management.
Mini Modbus Card	Supports Modbus communication with a PC via RS-485 and RS-232 interfaces,
(Part number: 3915101865-S)	allowing for flexible and simultaneous use.







Delta ICT LinkedIn









