Delta UPS – Agilon Family

VX Series. Line-interactive

600-1000 VA


Installation & Operation Quick Guide



Package Inspection


No.	Item	Q'ty
1	UPS	1 PC
2	Quick Guide	1 PC
3	USB Cable (only for 1000VA)	1 PC

Remove the UPS from its package and inspect it for damage that may have occurred during shipping. If any damage is discovered, re-pack the unit and return it to the place of purchase.





VХ



(Rear Panel)

00

No.	ltem	No.	ltem
0	LED Indicator	4	AC Input
0	ON/ OFF Button	6	Fuse
6	Output Socket	6	USB Port

Operation

• Placement


Install the UPS in a protected area that is free of excessive dust and has adequate air flow. Place the UPS away from other units at least 20 cm to avoid interference. For best performance, keep the indoor temperature between 0° C and 40° C.

Connect to Utility Power

Connect the AC power cord to the utility power. Then, the UPS will start to charge its inside battery (batteries). For best result, charge the battery (batteries) for 6 hours prior to initial use. It is not recommended to connect the UPS's AC power cord to any generator.

• Plug in Equipment

Plug your equipment to the Output Socket on the rear panel of the UPS. Note: Circuit Breaker rating of the Branch Circuit supplied from the Mains Input panel sizing must be 6A/250Vac for 600VA and 10A/250Vac for 1000VA in accordance with National electrical codes and standards.as per schematic (Based on N.E.C NFPA 70 -2014 ; Reference: Article 240)



WARNING:

1. Make sure that the UPS is powered on to protect all important devices from data loss during power failure.

2. NEVER connect a laser printer or scanner to the Output Socket of the UPS. The equipment may draw significant power to overload the UPS.

Connect to USB Port and Install Software

Connect one end of the supplied USB cable to your PC and the other to the USB port located at the rear of the UPS. Download the latest version of ViewPower software (http://www.deltapowersolutions.com/en/mcis/600va-1500va-single-phase-ups-vx-series-software-download.php) to your hard drive. Follow on-screen instructions to complete the software installation.


• Turn On/ Off the UPS


When the UPS is OFF, press the ON/ OFF Button to turn on the UPS and the LED will be on. When the UPS is ON, press the ON/ OFF Button to turn off the UPS and the LED will shut off.

Fuse Replacement

When the UPS always runs in battery mode, it might be because the fuse is damaged. If yes, please follow the following procedures to replace the fuse

 $|1\rangle$ Remove the fuse cover from the rear panel.





 $\left(3 \right)$ Replace the fuse cover back to the rear panel.

Storage

All connected equipment should be turned off and disconnected from the UPS to avoid battery drain. Unplug the UPS from the wall outlet and turn off the UPS for storage. Store the UPS unit covered and upright in the environment where the ambient temperature is -20°C to 50°C with its battery fully charged.



600VA Model

LED	Alarm	UPS Status
ON	OFF	The main AC power is normal and the UPS runs normally.
ON	Sounds all the time	UPS fault.
Flashing	Sounds every 10 seconds	Power failure occurs and the UPS runs in battery mode.
Flashing	Sounds every second	Low battery.
OFF	OFF	The UPS is off.

1000VA Model

LED	Alarm	UPS Status	
Green (On)	OFF	The main AC power is normal and the UPS runs normally.	
Red (On)	Continuously sounding	UPS fault.	
Yellow (flashing)	Sounds every 10 seconds	Power failure occurs and the UPS runs in battery mode.	
Yellow (flashing)	Sounds every second	Low battery.	
Green (Off)	OFF	The UPS is off.	

(5) Safety Caution

SAVE THESE INSTRUCTIONS-This guick guide contains important instructions that should be followed during installation and maintenance of the UPS and battery (batteries).

- The UPS utilizes voltage that may be hazardous. Do not attempt to disassemble the unit. The unit contains no user replaceable parts. Only factory service personnel may perform repairs.
- This pluggable type A equipment with battery (batteries) already installed by the supplier is operator installable and may be operated by laymen.



(600VA)

- The mains socket outlet that supplies the UPS shall be installed near the UPS and shall be easily accessible.
- During the installation of this equipment it should be assured that the sum of the leakage current of the UPS and the connected loads does not exceed 3.5mA.
- Connection to any other type of receptacle other than a two-pole, threewire grounded receptacle may result in shock hazard as well as violate local electrical codes.
- In the event of an emergency, press the ON/ OFF Button and disconnect the power cord from the AC power supply to properly disable the UPS.
- Do not allow any liquid or any foreign object to enter the UPS. Do not place beverages or any other liquid-containing vessels on or near the unit.
- The unit is intended for installation in a controlled environment (temperature controlled, indoor area free of conductive contaminants). Avoid installing the UPS in any location where there is standing or running water, or excessive humidity.
- Do not plug the UPS input into its own output.
- Do not attach a power strip or surge suppressor to the UPS.
- Do not attach non-computer-related items, such as medical equipment, life-support equipment, microwave ovens, or vacuum cleaners to the UPS.
- Do not dispose of battery (batteries) in a fire as they may explode.
- A battery can present a risk of electrical shock and high short circuit current. The following precautions should be observed when working on batteries:
- 1. Remove watches, rings, or other metal objects from the hands.
- 2. Use tools with insulated handles.
- 3. Wear rubber gloves and boots.
- 4. Do not lay tools or metal parts on top of battery (batteries).
- Disconnect charging source prior to connecting or disconnecting the terminals of battery (batteries).
- Internal battery voltage is 12Vdc. Battery type is sealed, lead-acid, 6-cell battery.
- Servicing of batteries should be performed or supervised by personnel knowledgeable of batteries and the required precautions. Keep unauthorized personnel away from batteries.
- When replacing battery (batteries), replace with the same number and type of sealed lead-acid battery (batteries).
- Do not open or mutilate the battery or batteries. Release electrolyte is harmful to the skin and eyes. It may be toxic.
- Attention! Hazardous through electric shock. Even disconnection of this unit from the mains, hazardous voltage still may be accessible through supply from the battery (batteries). The battery supply should be therefore disconnected in the plus and minus pole at the connectors of the battery (batteries) when maintenance or service work inside the UPS is necessary.
- To reduce the risk of overheating the UPS, do not cover the UPS's cooling vents and avoid exposing the unit to direct sunlight or installing the unit near heat emitting appliances such as heaters or furnaces.
- Unplug the UPS prior to cleaning and do not use liquid or spray detergent.

Troubleshooting

Problem	Possible Cause	Solutions
	The UPS is not on.	Press the ON/ OFF Button again to turn on the UPS.
LED doesn't illuminate	Battery voltage is too low.	Charge the battery (batteries) at least 6 hours.
	Battery fault.	Replace the battery (batteries).
The UPS	The power cord becomes loose.	Re-plug the power cord.
always runs in battery mode.	The fuse is damaged.	Replace the fuse. For how to replace the fuse, please refer to ③ Operation
The UPS continuously beeps.	Please check the Fault Code Table for the details.	Please check the Fault Code Table for the details.
	Battery voltage is too low.	Charge the battery (batteries) at least 6 hours.
Backup time is too short.	Overload.	Remove some unnecessary loads. Before reconnecting equipment, please verify that the load matches the UPS capability specified in the specs.
	Battery defect.	Replace the battery (batteries).

If any abnormal situations occur that are not listed above, please call for service immediately.

8) Technical Specifications

Model	600VA	1000VA	
Capacity	600VA/360W	1kVA/600W	
Nominal Input Voltage	230 Vac		
Input Voltage Range	140~300 Vac		
Output Voltage	230 Vac ± 10% (Bat. mode)		
Transfer Time	Typical 4 ~ 8 ms		
Waveform	Simulated Sine Wave		
Battery Type & No.	12V/7Ah x 1	12V/7Ah x 2	
Charging Time	Typical 4 ~ 6 hours		
Dimensions (D x W x H)	279 x 101 x 142 mm	320 x 130 x 182 mm	
Net Weight (kgs)	4.2	7.8	
Humidity	0 - 90% RH @ 0 - 40°C (non-condensing)		
Noise Level	Less than 40dB		

* Specifications are subject to change without notice.

9 Warranty

Seller warrants this product, if used in accordance with all applicable instructions, to be free from original defects in material and workmanship within the warranty period. If the product has any failure problem within the warranty period, Seller will repair or replace the product at its sole discretion according to the failure situation.

This warranty does not apply to normal wear or to damage resulting from improper installation, operation, usage, maintenance or irresistible force (i.e. war, fire, natural disaster, etc.), and this warranty also expressly excludes all incidental and consequential damages. Maintenance service for a fee is provided for any damage out of the warranty period. If any maintenance is required, please directly contact the supplier or Seller.

WARNING:

The individual user should take care to determine prior to use whether the environment and the load characteristic are suitable, adequate or safe for the installation and the usage of this product. The Quick Guide must be carefully followed. Seller makes no representation or warranty as to the suitability or fitness of this product for any specific application.

Copyright © 2018 by Delta Electronics Inc. All Rights Reserved. Changes may be made periodically to the information in this Quick Guide without obligation to notify any person of such revisions or changes.

