

Delta UPS-Amplon Family

RT Series

5/6/8/10 kVA, Single Phase; 15/20 kVA, Three Phase

A total solution for reliable power with high availability and performance

The Amplon RT Series 5-20kVA is an online double-conversion UPS that provides best-in-class designs in compact 2U size, high power density, system efficiency, and versatile configurations to fulfill customers' requirements. Unity output power factor maximizes capacity for more critical loads, while outstanding energy savings can be achieved based on the AC-AC efficiency of up to 96.5% and 99% in ECO mode. In addition, RT Series 5-20kVA UPS is the first in the market that offers standard Li-ion external battery cabinets, which deliver better power density and sustainability. Along with the parallel capacity of up to four units, the new series is the ideal small power UPS for mission-critical applications, such as servers, data centers, telecommunications, and manufacturing.

Availability & Flexibility

- True online double-conversion topology and zero transfer time to battery provides 24/7 full-time protection
- Wide input voltage range allows the UPS to operate in harsh electrical environments and extends battery life
- AC-start function allows the UPS to be switched on without connecting to a battery
- Programmable load bank disconnects non-critical loads when a blackout occurs and reserves more battery power for critical loads
- Up to four units parallel capacity allows redundancy and load expansion (Apply to 5-10kVA)
- Hot swappable batteries ensure continuous operation even when batteries are being replaced
- VRLA and Li-ion External Battery Cabinet (EBC) are available for scalable runtime
- Flexible battery quantity configuration enables optimized battery investment. And when one battery fails, it could be removed without replacing the entire battery string, reducing maintenance cost and efforts
- The Power Distribution Box (PDB) and Maintenance Bypass Breaker (MBB) are optional respectively for easy configuration and easy UPS replacement.
- The rRPP (Rack Remote Power Panel), which can be integrated with standard server racks, simplifies power output distribution and power monitoring
- Common battery configuration is supported in UPS parallel mode to save installation space and additional battery costs (Apply to 15/20 kVA)



Efficiency & Reliability

- Unity output power factor guarantees no de-rating with loads and provides permanent 100% kW
- Best-in-class AC-AC efficiency of up to 96.5% and 99% in ECO mode lowers energy costs
- Automatic fan speed control maximizes system efficiency and significantly reduces audible noise and prolongs battery life
- Fan failure detection sends early warnings to facilitate predictive maintenance of UPS

Manageability

- Intelligent battery management to extend battery life and maximize battery performance. The battery aging detection monitors battery status for predictive maintenance, and the 3-stage charging mechanism keeps the battery from continuous float charging during the intermission stage to prolong battery life
- Excellent local management through a user-friendly graphical and multi-lingual LCD display
- Various types of communication interfaces, including USB, RS-232, and RS-485 ports, mini slot, REPO/ROO for remote management, and in-built dry contacts for monitoring and notification of system operation conditions
- UPS management software such as ShutdownAgent and InfraSuite Device Manager allow users to monitor UPS status and protect critical devices



Server



Network



Banking



POS



Security

Delta UPS-Amplon Family

RT Series

5/6/8/10 kVA, Single Phase; 15/20 kVA, Three Phase

Technical Specifications

Model	RT-5K	RT-6K	RT-8K	RT-10K	RT-15K3P	RT-20K3P
Power Rating	5kVA/5kW	6kVA/6kW	8kVA/8kW	10kVA/10kW	15kVA/15kW	20kVA/20kW
Input	Voltage Range		100 ~ 280V (Single phase, 2-wire + G) 100 ~ 175V with linear de-rating 50 ~ 100%		138 ~ 485V (Three phase, 4-wire + G) 138 ~ 305V with linear de-rating 40 ~ 100%	
	Frequency		40 ~ 70 Hz			
	Power Factor		> 0.99 (full load)			
	iTHD		< 3%			
	Input connection		Input terminal x 1		Input terminal x 1, Bypass Input terminal x 1	
Output	Power Factor		Unity			
	Voltage		200, 208, 220, 230, 240 Vac (Single phase)		380/400/415 Vac (Three phase), or 220/230/240 Vac (Single phase)	
	Frequency		50/60Hz ±0.05Hz			
	Voltage Harmonic Distortion		≤ 2% (linear load)			
Overload Capability		≤ 105%: continuous; 106 ~ 125%, 5 min.; 126 ~ 150%, 1 min.; > 150%: 500ms		≤ 105%: continuous; 106 ~ 125%: 2 min.; 126 ~ 150%: 30 sec; > 150%: 200ms		
Receptacle	Terminal x 1 Load bank: Terminal x 1				Terminal x 1	
Efficiency	AC-AC		Up to 95.5%		Up to 96.5%	
	ECO Mode		Up to 99%			
Battery Voltage	5-10kVA: 144 Vdc*, 192 ~ 264 Vdc 15-20kVA: ±144 Vdc*, ±192 ~ 264 Vdc					
Charger Current	Up to 8A					
Typical Backup Time	Depending on different configurations required by customers					
Audible Noise	48 dB		50 dB		54 dB	
Display	Graphical and multi-lingual LCD					
Communication Interfaces	MINI Slot x 1, Parallel Port x 2, USB Port x 1, RS232 Port** x 1, RS485 Port x 1, REPO/ROO Port x 1, Dry Contact x 4					
Dimensions (W x D x H)	440 x 430 x 88.2 mm		440 x 565 x 88.2 mm		440 x 730 x 88.2 mm	
Weight	10.9 kg		10.9 kg		22 kg	
Environment	Operating Temperature		0 ~ 55° C***			
	Relative Humidity		5 ~ 95% (non-condensing)			

* De-rating to 70% load

** Not applicable to RT 20kVA

*** When the operating temperature is at 40 ~ 55° C, the UPS will be de-rated to 75% of its capacity

All specifications are subject to change without prior notice.



2007~ 2008 Forbes Asia's Fabulous 50



2009 Frost & Sullivan Green Excellence Award for Corporate Leadership



Delta's Manufacturing System Certified by ISO 9001 and ISO 14001 Standards



IECQ Certificate of Hazardous Substance Process Management

