

# GoCool-240

## Liquid-to-Air Coolant Distribution Unit

Unlock unmatched efficiency with Delta's Liquid-to-Air (L2A) CDU for HPC and AI workloads. L2A CDU provides a closed-loop liquid solution that eliminates the need for raised floors or extensive piping, and seamlessly integrates with direct-to-chip cooling for superior performance. Enjoy high cooling density, minimal power consumption, and simplified deployment. With customizable options, Delta's GoCool-240 can achieve up to 240 kW per rack, ensuring reliability with redundant components and hot-swappable features. The GoCool L2A CDU is ideal for data center retrofits and scalable growth.



### Superior Heat Dissipation

---

- Excellent thermal resistance that significantly outperforms air cooling
- Maximizes cooling density, providing more efficient heat removal

### Cost Efficient

---

- Ultra-efficient power usage: lower power consumption under 13%
- Seamless integration: no raised floors or facility piping needed; simplifies layout and adapts easily to specific requirements
- Optimizes space utilization: increases compute density and maximizes space without facility modifications
- Utilizes existing infrastructure: Room Cooling (CRAH), hot air containment and racks

### Robust Reliability

---

- Redundant design for key components: pump, fan, sensor and controller
- Assures coolant quality with integrated 50-micron filter
- Hot-swappable pump and fan enable swift onsite replacement

## Technical Specifications

<b>Model</b>	<b>GoCool-240</b>
Nominal Cooling Capacity	240 kW
<b>DEPLOYMENT</b>	
Ambient Temperature	35°C (95°F)
Airflow Rate	25,076 CFM
Coolant Supply Temperature	44°C (111.2°F)
Coolant Flow Rate	264 LPM
Coolant Supply Pressure	22.5 psi
Approach Temperature	9°C (16.2°F)
Coolant Feed Location	Front
<b>POWER SUPPLY</b>	
Nominal Power Supply Voltage	380/220 Vac, 3W+N+PE
Operating Voltage Range	346-480/200-277 Vac
Frequency	50/60 Hz
Maximum Power Consumption	28.7 kW
Dual Power Feed	Standard
<b>PHYSICAL</b>	
Dimensions (W x D x H)	1200 x 1352 x 2331 mm (47.3 x 53.3 x 91.8 in)
Net Weight	1320 kg (2910 lbs)
<b>COMMUNICATION INTERFACE</b>	
Display	LCD touchscreen
Protocols	Modbus RTU
<b>ENVIRONMENT</b>	
Operating Temperature	10 to 35°C (50 to 95°F)
Humidity	20-80%
<b>CONFORMANCE</b>	
Safety	UL
<b>FEATURES</b>	
Leak Detection	Standard
Networking Remote Monitoring/Control	Standard
Individual Fan Fail Sensing	Standard
Variable DC Fans	Standard

All specifications are subject to change without prior notice.



Delta Group - ICT BG



Delta ICT LinkedIn



Delta ICT YouTube

