

Delta InfraSuite Power Management

Rack Power Distribution Units

Integrated power distribution for optimal power management

Delta's rack power distribution units (rPDUs) provide optimal power distribution for devices inside a rack. In addition to easily distributing power to equipment, rPDUs also provide complete power protection. Delta offers a range of basic and metered rPDUs that you can install vertically or horizontally inside a rack. It makes establishing a data center more efficient.

Metered Rack PDU

Availability

- Tool-less installation in Delta's standard rack cabinets
- Brackets included for mounting in other brands' rack cabinets
- Zero-U installation saving valuable rack space
- Single or three phase input voltage available

Safety

- LED current (rms value) display and overload warning indicator
- Branch circuit breaker protection
- International standards of cables and power plugs/ receptacle

Management

- Upgradable firmware for maintaining optimal function
- Integrated with the InfraSuite management software
- Optional SNMP card for remote monitoring



Basic Rack PDU

Availability

- Tool-less installation in Delta's standard rack cabinets
- Brackets included for mounting in other brands' rack cabinets
- Vertical or horizontal mounting method, saving valuable rack space
- Single phase or three phase input voltage available

Safety

- Branch circuit breaker protection
- International standards of cables and power plugs/ receptacle



The amps and safety alarm indicators automatically adjust according to the position of the rPDU



Delta InfraSuite Power Management

Rack Power Distribution Units

Technical Specifications

Input Voltage / Phase	Rated Current	Plug Type	Output Voltage / Phase	Outputs (Number)	Dimensions (W x H x D)	Weight	Certificate	Model
Basic Rack PDU								
100-120Vac / 1	16A	NEMA L5-20P	100-120Vac / 1	NEMA 5-15/20R (8)	440 x 44 x 55mm	1.56kg	UL / cUL	PDU7111
	24A	NEMA L5-30P	100-120Vac / 1	NEMA 5-15/20R (24)	48 x 1250 x 50/90mm	4.88kg	UL / cUL	PDU5113
200-240Vac / 1	16A	NEMA L6-20P	200-240Vac / 1	IEC320 C13 (12)	440 x 44 x 55mm	1.64kg	UL / cUL	PDU7211
		IEC309-16A-3W	200-240Vac / 1	IEC320 C13 (12)	440 x 44 x 55mm	1.48kg	CE, CCC	PDU7311
	24A	NEMA L6-30P	200-240Vac / 1	IEC320 C13 (24)	48 x 1250 x 50/90mm	4.92kg	UL / cUL	PDU5213
		32A	IEC309-32A-3W	200-240Vac / 1	IEC320 C19 (4) IEC320 C13 (24)	48 x 1250 x 50/90mm	4.90kg	CE, CCC
200-240Vac / 3Δ	40A	CS8365C	200-240Vac / 1	IEC320 C13 (12)	55 x 1000 x 60/90mm	9.50kg	UL / cUL	PDUD526
Metered Rack PDU								
100-120Vac / 1	24A	NEMA L5-30P	100-120Vac / 1	NEMA 5-15/20R (24)	48 x 1250 x 50/90mm	5.34kg	UL / cUL	PDU1113
200-240Vac / 1	16A	IEC309-16A-3W	200-240Vac / 1	IEC320 C19 (3) IEC320 C13 (24)	48 x 1250 x 50/90mm	4.56kg	CE, CCC	PDU1311
		IEC309-20A-3W	200-240Vac / 1	IEC320 C13 (24)	48 x 1250 x 50/90mm	4.60kg	UL / cUL	PDU1211B
	24A	NEMA L6-30P	200-240Vac / 1	IEC320 C13 (24)	48 x 1250 x 50/90mm	5.24kg	UL / cUL	PDU1213
		IEC309-30A-3W	200-240Vac / 1	IEC320 C19 (4) IEC320 C13 (24)	48 x 1250 x 50/90mm	5.12kg	UL / cUL	PDU1313B
200-240Vac / 3Δ	28A	CS8365C	200-240Vac / 1	IEC320 C19 (6) IEC320 C13 (30)	55 x 1708 x 55mm	8.20kg	UL / cUL	AD-208/50B
			32A	CS8365C	200-240Vac / 1	IEC320 C19 (6) IEC320 C13 (30)	48 x 1780 x 50/100mm	9.00kg
				IEC320 C13 (36)	48 x 1560 x 50/100mm	8.00kg	UL / cUL	PDU2525
346-415Vac / 3Y	16A	IEC309-16A-5W	200-240Vac / 1	IEC320 C19 (3) IEC320 C13 (36)	48 x 1560 x 50/90mm	6.06kg	CE, CCC	PDU2421
		IEC309-20A-5W	200-240Vac / 1	IEC320 C19 (3) IEC320 C13 (36)	58 x 1750 x 60/100mm	6.86kg	UL / cUL	PDUE421B
	24A	IEC309-30A-5W	200-240Vac / 1					
	32A	IEC309-32A-5W	200-240Vac / 1	IEC320 C19 (3) IEC320 C13 (36)	48 x 1660 x 50/100mm	8.30kg	CE	PDU4425
				IEC320 C19 (3) IEC320 C13 (24)	48 x 1535 x 50/100mm	7.10kg	CE	PDU4425-M
	32A (UL 24A)	IEC309-32A-5W	200-240Vac / 1	IEC320 C19 (6) IEC320 C13 (30)	55 x 1708 x 55/70mm	8.00kg	UL / cUL, CE	AD-240/32J

Interface *	Function
RS232-1	Connect to a PC for remote operation or a firmware upgrade
RS232-2	Connect to an SNMP card or to another rPDUs

* For metered rack PDU

Environment	
Temperature	Operating: 0~45/50°C*, Storage: -20~65°C
Relative Humidity	Operating: 5~95%
Elevation	Operating: 0~2000m, Storage: 0~15000m

* 50°C only available for AD-XXX/XXX

