

Ultron DPM Gen2 Series UPS

Three-phase, 600-2500 kVA, 480 Vac

Uplevel Performance, Ensure Protection

Selected by leading global cloud providers, Delta's DPM Gen2 introduces advanced features for enhanced efficiency and reliability. This includes OPEX savings with up to 97.5% AC-AC efficiency and improved grid stability. Synchronized Multiple Bus (SMB) and parallel scalability ensures flawless reliability, making it the ideal solution for fortified hyperscale data centers.



OPEX Savings

- AC-AC efficiency up to 97.5%, efficiency optimization at light loads saves energy costs
- Clean mode (voltage independent mode) up to 99.2% efficient guarantees the optimum power condition while maintaining the highest level of efficiency
- Optimizes energy cost with off-peak charging, avoiding peak-time expense
- Elevates grid stability through responsive demand reduction and fast frequency regulation, triggers upon utility requests for eligible bill subsidies

Impeccable Reliability

- Assures smooth power transitions with integrated Synchronized Multiple Bus (SMB), minimizing transformer inrush currents and maintaining balanced power from dual sources
- Parallels up to 8 units for redundancy or expansion, supported by N+1 internal redundancy in power modular configuration
- Maximizes UPS performance and lifespan with self-diagnosis and key component analysis

Ultimate Availability

- Lithium-ion battery ready. Adjustable battery charging voltage adapts to multiple types of batteries
- Seamless power shifts to generator with an advance power walk-in function, pausing during frequency issues for smooth transitions without unnecessary generator sizing expansion
- Grid interactive application. Provides corrective operation for unstable renewal energy sources with an innovative topology design that handles grid and battery power at the same time
- Easy mounting/cabling that supports both top and bottom cable entry and full front access



IT



Telecom



Industrial



Transportation



Financial



Government



Technical Specifications

Model	DPM G2-	600K ⁽¹⁾	900K	1200K	1500K	1800K	2100K	2400K ⁽¹⁾	2500K	
Power Rating		600 kVA 600 kW	900 kVA 900 kW	1200 kVA 1200 kW	1500 kVA 1500 kW	1800 kVA 1800 kW	2100 kVA 2100 kW	2400 kVA 2400 kW	2500kVA 2500kW	
Parallel Configuration		Up to 8 units								
INPUT										
Nominal Voltage		480 Vac, 3P3W+PE								
Voltage Range		408-552 Vac (100% load)								
Frequency Range		40-70 Hz								
Total Harmonic Distortion (THDi)		< 3% (100% resistive load)								
Power Factor		> 0.99 (100% load)								
Short Circuit Withstand Rating		65 kA				100 kA				
OUTPUT										
Nominal Voltage		480 Vac, 3P3W+PE								
Voltage Regulation		±1% (static)								
Frequency		50/60 ±0.05 Hz								
Total Harmonic Distortion (THDv)		< 1% (linear load)								
Overload Capability		< 110%: continues; 110-125%: 10 mins; 126-150%: 1 min; > 150%: 1 sec								
Current Crest Ratio		3:1								
EFFICIENCY										
Online Mode		Up to 97.5%								
Clean Mode (VI)		Up to 99.2%								
BATTERY										
Battery Type		VRLA/Vented lead-acid/Lithium-ion/Ni-Zinc								
Nominal Voltage		480 Vdc								
Quantity		34-35 ⁽²⁾ , 36-46 pcs (Configurable, 12V VRLA battery)								
Charge Current		* ⁽³⁾	375 A	500 A	625 A	750 A	1000 A	* ⁽³⁾	1125 A	
Protection Design		Battery shunt trip x1, Battery temperature detection x4, Battery breaker status dry contact x1								
COMMUNICATION INTERFACE										
Display		10-inch color touchscreen								
Port		Smart slot x2, Modbus (RS-485) port x1, REPO port x1, Input dry contact x6, Output dry contact x6, Synchronized Multiple Bus (SMB) x2, Breaker status detection x4, EMS/Console port x1, Ethernet x1								
Protocols		SNMP, Modbus RTU, Modbus TCP/IP, HTTP(S), SNMP, SMTP, BOOTP, DHCP								
PHYSICAL										
Dimensions (W x D x H)		* ⁽³⁾	2710 x 990 x 2000 mm	3070 x 990 x 2000 mm	3400 x 990 x 2000 mm	4530 x 990 x 2000 mm	4870 x 990 x 2000 mm	* ⁽³⁾	5903 x 990 x 2000 mm	
Net Weight		* ⁽³⁾	2026 kg	2408 kg	2779 kg	4174 kg	4551 kg	* ⁽³⁾	5820 kg	
ENVIRONMENT										
Operating Temperature		0 to 40°C								
Humidity		0-95% (non-condensing)								
Altitude		0-2000 m (derating 1%/100m from 1001-2000 m)								
CONFORMANCE										
Safety		UL								
EMC		FCC Class A								
Performance		IEC 62040-3								
Sustainability		RoHS, REACH, Energy Star 2.0								
FEATURES										
Standard		Advance power walk-in for generator, Backfeed protection with contactor, Burn-in test without load bank, Cold start function, Synchronized multiple bus (SMB), Battery shunt trip, Auxiliary power 48 Vdc for shunt trip, Failure prediction								
Optional		Grid interactive, Software integration with Delta Lithium-ion battery BMS, DC battery ground fault detector, Integrated battery switch cabinet, IR scan window								

(1) Upcoming product

(2) 34-35 pcs require service setting and load derating

(3) To be released

All specifications are subject to change without prior notice.



Delta Data Center



Delta ICT LinkedIn



Delta ICT YouTube

