

Ultron DPM Gen2 Series UPS

Three-phase, 250-1750 kVA, 400 Vac

Uplevel Performance, Ensure Protection

Selected by leading global cloud providers, Delta's DPM Gen2 introduces advanced features for enhanced efficiency and reliability. This includes OPEX savings with up to 97.3% AC-AC efficiency and improved grid stability. Synchronized Multiple Bus (SMB) and parallel scalability ensures flawless reliability, making it the ideal solution for fortified hyperscale data centers.



OPEX Savings

- AC-AC efficiency up to 97.3%, efficiency optimization at light loads saves energy costs
- Clean mode (voltage independent mode) up to 99% efficient guarantees the optimum power condition while maintaining the highest level of efficiency
- Optimizes energy cost with off-peak charging, avoiding peak-time expense
- Elevates grid stability through responsive demand reduction and fast frequency regulation, triggers upon utility requests for eligible bill subsidies

Impeccable Reliability

- Assures smooth power transitions with integrated Synchronized Multiple Bus (SMB), minimizing transformer inrush currents and maintaining balanced power from dual sources
- Parallels up to 8 units for redundancy or expansion, supported by N+1 internal redundancy in power modular configuration
- Maximizes UPS performance and lifespan with self-diagnosis and key component analysis

Ultimate Availability

- Lithium-ion battery ready. Adjustable battery charging voltage adapts to multiple types of batteries
- Seamless power shifts to generator with an advance power walk-in function, pausing during frequency issues for smooth transitions without unnecessary generator sizing expansion
- Grid interactive application. Provides corrective operation for unstable renewal energy sources with an innovative topology design that handles grid and battery power at the same time
- Easy mounting/cabling that supports both top and bottom cable entry and full front access



IT



Telecom



Industrial



Transportation



Financial



Government



Technical Specifications

Model	DPM G2-	250K	500K ⁽¹⁾	750K ⁽¹⁾	1000K	1250K	1500K ⁽¹⁾	1750K ⁽¹⁾
Power Rating		250 kVA 250 kW	500 kVA 500 kW	750 kVA 750 kW	1000 kVA 1000 kW	1250 kVA 1250 kW	1500 kVA 1500 kW	1750 kVA 1750 kW
Parallel Configuration		Up to 8 units						
INPUT								
Nominal Voltage		380/400/415 Vac, 3P3W+PE or 3P4W+PE						
Voltage Range		323-477 Vac (100% load)						
Frequency Range		40-70 Hz						
Total Harmonic Distortion (THDi)		< 3% (100% resistive load)						
Power Factor		> 0.99 (100% load)						
Short Circuit Withstand Rating		65 kA			100 kA			
OUTPUT								
Nominal Voltage		380/400/415 Vac, 3P3W+PE or 3P4W+PE						
Voltage Regulation		±1% (static)						
Frequency		50/60 ± 0.05 Hz						
Total Harmonic Distortion (THDv)		< 1% (linear load)						
Power Factor		1						
Overload Capability		< 110%: continues; 110-125%: 10 mins; 126-150%: 1 min; > 150%: 1 sec						
Current Crest Ratio		3:1						
EFFICIENCY								
Online Mode		Up to 97.3%						
Clean Mode (VI)		Up to 99%						
BATTERY								
Battery Type		VRLA/Vented lead-acid/Lithium-ion/Ni-Zinc						
Nominal Voltage		480 Vdc						
Quantity		34-35 ⁽²⁾ , 36-46 pcs (Configurable, 12V VRLA battery)						
Charge Current		125 A	*(3)	*(3)	500 A	625 A	*(3)	*(3)
Protection Design		Battery shunt trip x1, Battery temperature detection x4, Battery breaker status dry contact x1						
COMMUNICATION INTERFACE								
Display		10-inch color touchscreen						
Port		Smart slot x2, Modbus (RS-485) port x1, REPO port x1, Input dry contact x6, Output dry contact x6, Synchronized Multiple Bus (SMB) x2, Breaker status detection x4, EMS/Console port x1, Ethernet x1						
Protocols		SNMP, Modbus RTU, Modbus TCP/IP, HTTP(S), SNTP, SMTP, BOOTP, DHCP						
PHYSICAL								
Dimensions (W x D x H)		1030 x 990 x 2000 mm	*(3)	*(3)	3070 x 990 x 2000 mm	3400 x 990 x 2000 mm	*(3)	*(3)
Net Weight		676 kg	*(3)	*(3)	2450 kg	2836.3 kg	*(3)	*(3)
ENVIRONMENT								
Operating Temperature		0 to 40°C						
Humidity		0-95% (non-condensing)						
Altitude		0-2000 m (derating 1%/100m from 1001-2000 m)						
CONFORMANCE								
Safety		CE, UL						
EMC		IEC 62040-2, FCC Class A						
Performance		IEC 62040-3						
Sustainability		RoHS, REACH, Energy Star 2.0 ⁽⁴⁾						
FEATURES								
Standard		Advance power walk-in for generator, Backfeed protection with contactor, Burn-in test without load bank, Cold start function, Synchronized multiple bus (SMB), Frequency conversion, Battery shunt trip, Auxiliary power 48 Vdc for shunt trip, Failure prediction						
Optional		Grid interactive, Software integration with Delta Lithium-ion battery BMS, DC battery ground fault detector, Integrated battery switch cabinet, IR scan window						

(1) Upcoming product

(2) 34-35 pcs require service setting and load derating

(3) To be released

(4) Meets Energy Star 2.0 efficiency standards by design

All specifications are subject to change without prior notice.



Delta Data Center



Delta ICT LinkedIn



Delta ICT YouTube

