

Agilon VX Series UPS

Single-phase, 600-1500 VA, 230 Vac

Reliable power protection for small business and home office applications

The Agilon VX series line-interactive UPS designed with microprocessor control offers reliable and cost-effective power protection for PCs, monitors, POS, and other sensitive electronics used in home offices and small businesses. The integrated Automatic Voltage Regulation (AVR) ensures all electronics are receiving stable power while providing higher availability. The Agilon VX series' LCD display, auto-shutdown software and other superior features make these units perfect for your data protection.



Reliability

- The integrated AVR (Automatic Voltage Regulation) stabilizes the output voltage for better power quality
- Excellent microprocessor control enables accurate detection of power frequency for higher reliability
- Wide input voltage range allows the UPS to work in harsh electrical environments and reduces battery discharging time
- Batteries automatically recharge even when the UPS is in off mode and the UPS can start without mains (Cold-Start)
- UPS restarts automatically while utility power is recovering
- Surge protection defends your critical load against damage

Convenience

- IEC 60320 or universal output socket options offer greater installation flexibility and enable easy integration with computers and IT peripherals
- Compact size saves more space for critical equipment

Manageability

- Standard USB communication port enhances monitoring and manageability
- Touch screen LCD for a clear display of UPS information (Only applicable for LCD models)
- Advanced UPS management software provides remote shutdown and control



SME



Retail



Technical Specifications

Model		VX-600VA	VX-1000VA	VX-1500VA
Topology		Line interactive		
Power Rating		600 VA 360 W	1000 VA 600 W	1500 VA 900 W
INPUT				
Nominal Voltage		230 Vac, 1P2W+PE		
Voltage Range		170-280 Vac (100% load)		
Frequency Range		45-65 Hz		
Plug Type ⁽¹⁾		IEC		
OUTPUT				
Nominal Voltage		230 Vac, 1P2W+PE		
Voltage Regulation		±10%		
Frequency		50/60 ± 1 Hz		
Power Factor		0.6		
Connection ⁽²⁾	IEC Model	IEC C13 x4		
	Universal Model	IEC C13 x2 + Universal x2	Universal x3	
Overload Capability		110 ± 10%: < 5 mins		
EFFICIENCY				
Online Mode		Up to 95%		
BATTERY				
Battery Type		VRLA		
Nominal Voltage		12 Vdc	24 Vdc	
Quantity		1 pcs	2 pcs	
Runtime ⁽³⁾		5.7 mins	5 mins	5.5 mins
Recharge Time		6-8 hours to 90%		
COMMUNICATION INTERFACE				
Display		LED indicator	LCD touch panel	
Port		USB		
Audible Alarm		Battery mode, Low battery, Overload, Fault		
PHYSICAL				
Dimensions (W x D x H)		101 x 279 x 142 mm	130 x 320 x 182 mm	
Net Weight		4.2 kg	8.2 kg	9.7 kg
Packing Dimensions (W x D x H)		140 x 344 x 220 mm	192 x 390 x 275 mm	
Packing Weight		4.5 kg	8.9 kg	10.4 kg
ENVIRONMENT				
Operating Temperature		0 to 40°C		
Humidity		0-95% (non-condensing)		
Audible Noise		< 40 dBA		< 45 dBA
Altitude		0-1000 m		
Storage Temperature		-20 to 50°C		
CONFORMANCE				
Safety		CE, UKCA, EAC, TISI, RCM, BIS, KC		
Sustainability		RoHS, REACH		

(1) Models with Australian, Korean, Indian, and Schuko input plugs are also available

(2) Options include Schuko, AU and IN output connections

(3) Runtime with 50% load

All specifications are subject to change without prior notice.



Delta Data Center



Delta ICT LinkedIn



Delta ICT YouTube

